

Han 3A Housing Angled bulkhead mounting



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 20 003 0811 |
| Specification | Han 3A Housing Angled bulkhead mounting |
| HARTING eCatalogue | https://b2b.harting.com/09200030811 |

Identification

| | |
|-----------------------------|---|
| Category | Hoods/Housings |
| Series of hoods/housings | Han A [®] |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | Angled 4 fixing screws Square mounting flange |

Version

| | |
|----------------------|---|
| Locking type | Single locking lever |
| Size | 3 A |
| Field of application | Standard Hoods/housings for industrial applications |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP44 IP65 / IP67 with seal screw 09 20 000 9918 |
| Type rating acc. to UL 50 / UL 50E | 12 |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |
| Material (seal) | NBR |
| Material (locking) | Steel |



Pushing Performance

Material properties

| | |
|-----------------------------|-------------|
| Surface (locking) | Zinc plated |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
| CE | Yes |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 92 g |
| Country of origin | China |
| European customs tariff number | 85389099 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09200030811