

Han 24M-Metal Cover-DL-Seal-for Hood



Image is for illustration purposes only. Please refer to product description.

Part number	09 37 024 5402
Specification	Han 24M-Metal Cover-DL-Seal-for Hood
HARTING eCatalogue	https://b2b.harting.com/09370245402

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Protection cover
Description of hood/housing	for hoods
	Metal
	With fixing cord
Type	Low construction
	High construction

Version

Locking type	Double locking lever
Size	24 B
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	140.4 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09370245402YYC