

D-Sub, FE AWG 20-24 crimp cont



Part number	09 67 000 8476
Specification	D-Sub, FE AWG 20-24 crimp cont
HARTING eCatalogue	https://b2b.harting.com/09670008476

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts
Performance level	1

Technical characteristics

Conductor cross-section	0.25 ... 0.52 mm ²
Conductor cross-section	AWG 24 ... AWG 20
Contact resistance	≤10 mΩ
Stripping length	4 mm

Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	100
Net weight	0.22 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09670008476](#)