

Han-Yellock 10 cover f. housing w. seal



Image is for illustration purposes only. Please refer to product description.

Part number	11 20 003 5406
Specification	Han-Yellock 10 cover f. housing w. seal
HARTING eCatalogue	https://b2b.harting.com/11200035406

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings Thermoplastic With seal

Version

Size	Han-Yellock® 10
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	15.16 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

11200035406