

Han CGM-M M20x1,5 D.5-9mm/6-12mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5081
Specification	Han CGM-M M20x1,5 D.5-9mm/6-12mm
HARTING eCatalogue	https://b2b.harting.com/19000005081

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-M
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	22
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M20
Clamping range	5 ... 12 mm
Width across corners	24.4 mm

Material properties

Material (seal)	NBR
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780
	CSA-C22.2 No. 18.3 QCRV7.E479780

Commercial data

Packaging size	10
Net weight	29.8 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

19000005081