

## Han CGM-P M20x1,5 D.5-9mm black



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5181
Specification	Han CGM-P M20x1,5 D.5-9mm black
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005181">https://b2b.harting.com/19000005181</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-P
Type of accessory	Cable gland

### Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	≤4.5 Nm (depending on the cable and the seal insert used)
Wrench size	24
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M20
Clamping range	5 ... 9 mm
Width across corners	26.4 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780

## Commercial data

Packaging size	10
Net weight	11.7 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27144432 Screwed cable gland (electr.)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19000005181](#)