



Loading-Plan:

1	brown
2	blue
3	black
4	black

- Protection level: IP67
- Temperature range: -25°C ... +80°C



length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

4.0 to 40	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

Part no.	213481003XXXXXX
----------	-----------------

Type of cable	XX
PVC grey, 3x0.25mm ²	XX=80
PUR black, 3x0.25mm ²	XX=88

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.					
		All rights reserved		Created by TAMAS		Inspected by AVRAM		Standardisation HOFFMANN		Date 2014-07-01		State Final Release	
		Department EC PD - RO		Title M8 Cable Assembly								Doc-Key / ECM-Nr. 100577583/UGD/009/A 500000076586	
		HARTING Electronics GmbH D-32339 Espelkamp		Type TB		Number 213481003XXXXX						Rev. A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21348100388030](#)