

1		2		3		4		5		6		7		8	
Cont. No.	Part - no.	Type of cable		Dim. a[m]		Cont. No.	Part - no.	Type of cable		Dim. a[m]					
A	1	09475656001		0.5		45	09475656061			0.5					
	2	09475656002		1		46	09475656062			1					
	3	09475656003		1.5		47	09475656063			1.5					
	4	09475656004		2		48	09475656064			2					
	5	09475656005		3		49	09475656065			3					
B	6	09475656006		4		50	09475656066			4					
	7	09475656007		5		51	09475656067			5					
	8	09475656008		6		52	09475656068			6					
	9	09475656009		7		53	09475656069			7					
	10	09475656010		8		54	09475656070			8					
C	11	09475656011		9		55	09475656071			9					
	12	09475656012		10		56	09475656072			10					
	13	09475656013		15		57	09475656073			15					
	14	09475656014		20		58	09475656074			20					
	15	09475656015		30		59	09475656075			30					
D	16	09475656016		40		60	09475656076			40					
	17	09475656017		50		61	09475656077			50					
	18	09475656018		60		62	09475656078			60					
	19	09475656019		70		63	09475656079			70					
	20	09475656020		80		64	09475656080			80					
E	21	09475656021		90		65	09475656081			90					
	22	09475656022		100		66	09475656082			100					
	23	09475656031		0.5		67	09475656091			0.5					
	24	09475656032		1		68	09475656092			1					
	25	09475656033		1.5		69	09475656093			1.5					
F	26	09475656034		2		70	09475656094			2					
	27	09475656035		3		71	09475656095			3					
	28	09475656036		4		72	09475656096			4					
	29	09475656037		5		73	09475656097			5					
	30	09475656038		6		74	09475656098			6					
G	31	09475656039		7		75	09475656099			7					
	32	09475656040		8		76	09475656100			8					
	33	09475656041		9		77	09475656101			9					
	34	09475656042		10		78	09475656102			10					
	35	09475656043		15		79	09475656103			15					
H	36	09475656044		20		80	09475656104			20					
	37	09475656045		30		81	09475656105			30					
	38	09475656046		40		82	09475656106			40					
	39	09475656047		50		83	09475656107			50					
	40	09475656048		60		84	09475656108			60					
I	41	09475656049		70		85	09475656109			70					
	42	09475656050		80		86	09475656110			80					
	43	09475656051		90		87	09475656111			90					
	44	09475656052		100		88	09475656112			100					
		</													

	1	2	3	4	5	6	7	8			
A	Cont. No.	Part - no.	Type of cable		Dim. a[m]						
	89	094 75656161	HARTING PROFINET Type C Torsional Stress Cable, 4xAWG22/19 Cat. 5, PUR		0.5						
	90	094 75656162			1						
	91	094 75656163			1.5						
	92	094 75656164			2						
	93	094 75656165			3						
	94	094 75656166			4						
	95	094 75656167			5						
	96	094 75656168			6						
	97	094 75656169			7						
	98	094 75656170			8						
	99	094 75656171			9						
	100	094 75656172			10						
	101	094 75656173			15						
	102	094 75656174			20						
	103	094 75656175			30						
	104	094 75656176			40						
	105	094 75656177			50						
	106	094 75656178			60						
	107	094 75656179			70						
	108	094 75656180			80						
	109	094 75656181			90						
	110	094 75656182			100						
D											
E											
F											
					 All rights reserved Department EC PD - RO HARTING Electronics GmbH D-32339 Espelkamp Scale 1:1 Free size tol. Created by TOMUTA Inspected by AVRAM Standardisation HOFFMANN Date 2014-08-01 State Final Release Title RJ Industrial Cable Assembly Type TB Number 094 75656XXX Rev. B Page 3/3 Doc-Key / ECM-Nr. 100155397/UGD/006/B 500000078159						
	1	2	3	4	5	6	7	8			

		All Dimensions in mm Original Size DIN A3		Scale 1:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by TOMUTA		Inspected by AVRAM		Standardisation HOFFMANN		Date 2014-08-01		State Final Release			
		Department EC PD - RO		Title RJ Industrial Cable Assembly								Doc-Key / ECM-Nr. 100155397/UGD/006/B 500000078159			
HARTING Electronics GmbH D-32339 Espelkamp				Type TB		Number 09475656XXX						Rev. B		Page 3/3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09475656012](#) [09475656067](#) [09475656074](#) [09475656007](#) [09475656042](#) [09475656097](#) [09475656104](#)
[09475656005](#) [09475656035](#) [09475656065](#) [09475656072](#) [09475656095](#) [09475656102](#) [09475656014](#) [09475656037](#)
[09475656044](#) [09475656093](#) [09475656003](#) [09475656033](#) [09475656063](#)