




Connector Location A

Connector Location B



NOTE:

For lengths < 1.0m:

- relative positioning of the connectors to each other will be as presented in the drawing, however with an admissible angular deviation around cable axis of $\pm 30^\circ$

For lengths ≥ 1.0 m:



-relative positioning of the connectors to each other not obligatory

* Ethernet transmission possible for lengths up to 45m

Temperature range:

- Fixed installation: $-30^\circ\text{C} \dots +75^\circ\text{C}$

- Dynamic installation: $-5^\circ\text{C} \dots +50^\circ\text{C}$

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing							
		All rights reserved		Created by MUNTEANV		Inspected by COSTEA		Standardisation AVRAM		Date 2017-10-31		State Final Release			
Department HCS - RO		Title RJ Industrial Cable Assembly								Doc-Key / ECM-Nr. 100170398/UGD/012/M 5000000126207					
HARTING Customised Solutions		Type TB		Number 094747471XX								Rev. M		Page 1/2	
D-32427 Minden															

1		2		3		4		5		6		7		8		
A	53	094 74 74 7136		4x2xAWG27/7, S/FTP, PUR, Cat.7, yellow		31		±1%								A
	52	094 74 74 7125				30										
	51	094 74 74 7182				28										
	50	094 74 74 7126				25										
	49	094 74 74 7181				22										
	48	094 74 74 7123				20										
	47	094 74 74 7179				19										
	46	094 74 74 7178				18										
B	45	094 74 74 7177				17										
	44	094 74 74 7124				16										
	43	094 74 74 7122				15										
	42	094 74 74 7134				14										
	41	094 74 74 7133				13.5										
	40	094 74 74 7176				13										
	39	094 74 74 7132				12.5										
	38	094 74 74 7131				12										
C	37	094 74 74 7130				11.5										
	36	094 74 74 7129				11										
	35	094 74 74 7121				10										
	34	094 74 74 7128				9.5										
	33	094 74 74 7120				9										
	32	094 74 74 7127				8.5										
	31	094 74 74 7119				8										
	30	094 74 74 7118				7.5										
D	29	094 74 74 7117				7										
	28	094 74 74 7174				6.5										
	27	094 74 74 7116				6										
	26	094 74 74 7173				5.5										
	25	094 74 74 7115				5										
	24	094 74 74 7172				4.75										
	23	094 74 74 7171				4.5										
	22	094 74 74 7170				4.25										
E	21	094 74 74 7114				4										
	20	094 74 74 7169				3.75										
	19	094 74 74 7168				3.5										
	18	094 74 74 7167				3.25										
	17	094 74 74 7113				3										
	16	094 74 74 7140				2.75										
	15	094 74 74 7112				2.5										
	14	094 74 74 7139				2.25										
F	13	094 74 74 7111				2										
	12	094 74 74 7138				1.75										
	11	094 74 74 7110				1.5										
	10	094 74 74 7137				1.25										
	9	094 74 74 7109		1												
	8	094 74 74 7108		0.9												
	7	094 74 74 7107		0.8												
	6	094 74 74 7106		0.7												
	5	094 74 74 7105		0.6												
	4	094 74 74 7104		0.5												
	3	094 74 74 7103		0.4												
	2	094 74 74 7102		0.3												
	1	094 74 74 7101		0.2												
	Cont. no.	Part no.		Type of cable		Dim. a[m]										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09474747108