

har-modular shell housing 60 1Set



Image is for illustration purposes only. Please refer to product description.

Part number	02 09 500 2060 200
Specification	har-modular shell housing 60 1Set
HARTING eCatalogue	https://harting.com/02095002060200

Identification

Category	Accessories
Series	har-modular®
Type of accessory	Shell housing

Version

Version	Top/side entry
Strain relief	With cable tie
Locking type	Locking lever
2 parts	Yes
Separable	Yes

Technical characteristics

Limiting temperature	-55 ... +125 °C
Degree of protection acc. to IEC 60529	IP20
Isolation group	III

Material properties

Material (hood/housing)	Thermoplastic resin (PC) Fibre-glass reinforced
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
Length	60.96 mm
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	1
Net weight	31.93 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140436398
eCl@ss	27440292 Connector component (accessories)
UNSPSC 24.0	39121400

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[02095002060200](#)