

Uni-Dicht-Verschr. Pg21, 20,5-17,0mm sw



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5158
Specification	Uni-Dicht-Verschr. Pg21, 20,5-17,0mm sw
HARTING eCatalogue	https://b2b.harting.com/09000005158

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods for cable to cable housing

Technical characteristics

Tightening torque	≤8 Nm (depending on the cable and the seal insert used)
Wrench size	33
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65
Size	Pg 21
Clamping range	17 ... 20.5 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

Commercial data

Packaging size	10
Net weight	10.4 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140001992
ETIM	EC003608
eCl@ss	27140807 Additional components cable gland

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09000005158](#)