

## har-SAB M12/8/5p PAC 5m PVC



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 07 001 2225 1  |
| Specification      | har-SAB M12/8/5p PAC 5m PVC   |
| HARTING eCatalogue | <a href="https://harting.com/090700122251">https://harting.com/090700122251</a> |

### Identification

|               |   |
|---------------|---|
| Series        | Circular connectors M12                             |
| Element       | Distribution boxes                                  |
| Specification | Pre-assembled master cable<br>With LED green/yellow |

### Version

|                       |                        |
|-----------------------|------------------------|
| Cable length          | 5 m                    |
| Core structure        | 3x AWG 18 + 16x AWG 22 |
| Total number of ports | 8                      |
| Number of contacts    | 5                      |

### Technical characteristics

|  |                    |
|--|--------------------|
| Rated current                          | 9 A                |
| Rated voltage                          | 10 V DC<br>30 V DC |
| Limiting temperature                   | -30 ... +85 °C     |
| Degree of protection acc. to IEC 60529 | IP67               |
| Number of channels per port            | 2                  |
| Circuit logic                          | PNP                |

### Material properties

|                  |           |
|------------------|-----------|
| Material (cable) | PVC       |
| RoHS             | compliant |
| ELV status       | compliant |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Yes           |
| California Proposition 65 substances | Nickel        |

## Specifications and approvals

|          |                         |
|----------|-------------------------|
| UL / CSA | UL 2238 CYJV.E500416    |
|          | CSA-C22.2 CYJV7.E500416 |

## Commercial data

|                                |   |
|--------------------------------|---|
| Packaging size                 | 1   |
| Country of origin              | China   |
| European customs tariff number | 85371098  |
| GTIN                           | 5713140277342   |
| ETIM                           | EC002585  |
| eCl@ss                         | 27440108 Passive Sensor-Actuator-Interface (with cable) |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[090700122251](#) [90700122251](#)