




Pushing Performance

Han-Fast Lock 4-6mm² m.Pin Ag Ro 2300St.



Part number	09 08 000 6123
Specification	Han-Fast Lock 4-6mm ² m.Pin Ag Ro 2300St.
HARTING eCatalogue	https://b2b.harting.com/09080006123

Identification

Category	Contacts
Series	Han-Fast [®] Lock
Type of contact	PCB contact
Description of the contact	With pin

Version

Pack contents	2300 pieces on reel
---------------	---------------------

Technical characteristics

Conductor cross-section	4 ... 6 mm ²
Operating current	≤60 A
Contact resistance	≤2 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (locking)	Copper alloy
Surface (locking)	Passivated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	9,120 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09080006123