




Pushing Performance

## Han Fast-Lock 10qmm ang.silverplate.+pin



Part number	09 08 000 7224
Specification	Han Fast-Lock 10qmm ang.silverplate.+pin
HARTING eCatalogue	<a href="https://b2b.harting.com/09080007224">https://b2b.harting.com/09080007224</a>

### Identification

Category	Contacts
Series	Han-Fast <sup>®</sup> Lock
Type of contact	PCB contact
Description of the contact	With pin Angled

### Version

Pack contents	Single contact
---------------	----------------

### Technical characteristics

Conductor cross-section	10 mm <sup>2</sup>
Operating current	≤60 A
Contact resistance	≤2 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (locking)	Copper alloy
Surface (locking)	Passivated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

## Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Lead

## Commercial data

Packaging size	100
Net weight	2.46 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09080007224