

Han TC300 female contact M8, short



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6679
Specification	Han TC300 female contact M8, short
HARTING eCatalogue	https://harting.com/09110006679

Identification

Category	Contacts
Series	TC 300
Type of contact	Screw contact
Description of the contact	M8 Short version

Version

Termination method	Screw termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤300 A
Contact resistance	≤0.3 mΩ
Tightening torque	10 Nm
Wrench size	5 14
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	47.074 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188549
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09110006679](#)