

Han Q 2/0-f HV 1.5sqmm




Image is for illustration purposes only. Please refer to product description.

Part number	09 12 002 2756
Specification	Han Q 2/0-f HV 1.5sqmm
HARTING eCatalogue	https://b2b.harting.com/09120022756

Identification

Category	Inserts
Series	Han® Q
Identification	2/0 High Voltage

Version

Termination method	Axial screw termination
Gender	Female
Size	3 A
Number of contacts	2
PE contact	Yes
Pack contents	With heat shrink tube

Technical characteristics

Conductor cross-section	1.5 ... 2.5 mm²
Rated current	40 A
Rated voltage	830 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤1 mΩ
Tightening torque	1.8 Nm



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	26.2 g
Country of origin	Germany
European customs tariff number	85366990



Pushing Performance
Since 1945

Commercial data

GTIN	5713140016675
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09120022756](#)