

Pneumatic contact male 3,0 mm



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 14 000 6152 |
| Specification | Pneumatic contact male 3,0 mm |
| HARTING eCatalogue | https://harting.com/09140006152 |

Identification

| | |
|----------------------------|------------------------------|
| Category | Contacts |
| Type of contact | Pneumatic contact |
| Description of the contact | Without shut-off Straight |

Version

| | |
|-----------------------|-----------------|
| Gender | Male |
| Manufacturing process | Turned contacts |

Technical characteristics

| | |
|----------------------|----------------|
| Limiting temperature | -40 ... +80 °C |
| Operating pressure | ≤8 bar |
| Tube inner diameter | 3 mm |

Material properties

| | |
|-----------------------------|---------------|
| Material (contacts) | Delrin acetal |
| Material (seal) | Buna-N |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |

Material properties

REACH SVHC substances Not contained

Specifications and approvals

| | |
|----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
|----------|--|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 0.6 g |
| Country of origin | Germany |
| European customs tariff number | 39269097 |
| GTIN | 5713140018273 |
| ETIM | EC000796 |
| eCl@ss | 27440204 Contact for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140006152](#)