

Han-Modular coax F-contact 50Ohm (RG58)




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6215
Specification	Han-Modular coax F-contact 50Ohm (RG58)
HARTING eCatalogue	https://harting.com/09140006215

Identification

Category	Contacts
Type of contact	Coaxial contact
Description of the contact	for cables RG 58

Version

Termination method	Solder / solder termination
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤1.5 A
Impedance coaxial	50 Ω

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance
Since 1945

Material properties

ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	2.8 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140018358
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140006215](#)