



Pushing Performance  
Since 1945

# Han RJ45 module, male for plugs



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 4622
Specification	Han RJ45 module, male for plugs
HARTING eCatalogue	<a href="https://b2b.harting.com/09140014622">https://b2b.harting.com/09140014622</a>

## Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® RJ45 module
Size of the module	Single module

## Version

Gender	Male
Number of contacts	8
Details	for data connectors

## Technical characteristics

Rated current	1 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +70 °C
Mating cycles	$\geq 500$

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)



**Pushing Performance**  
Since 1945

## Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019430
ETIM	EC002312
eCI@ss	27440207 Adapter for industrial connectors (module/contact insert)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140014622](#)