

# Han 40A PCB module, male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 2603
Specification	Han 40A PCB module, male
HARTING eCatalogue	<a href="https://b2b.harting.com/09140022603">https://b2b.harting.com/09140022603</a>

## Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	In the Han <sup>®</sup> 40 A Axial module

## Version

Gender	Male
--------	------

## Technical characteristics

Rated current	40 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

## Material properties

Material (insert)	Polycarbonate (PC)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Commercial data

Packaging size	2
Net weight	24.1 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019607
ETIM	EC000438
eCl@ss	27440217 Module for industrial connectors (power/signals)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140022603](#)