

Han HV single module, 16A 2500V male



Part number	09 14 002 3025
Specification	Han HV single module, 16A 2500V male
HARTING eCatalogue	https://b2b.harting.com/09140023025

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] HV module
Size of the module	Single module

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	2
Details	Please order crimp contacts separately.
Pack contents	1 module
	2 locking sleeves
	2 heat shrink tubes

Technical characteristics

Conductor cross-section	0.14 4 mm²
Wire outer diameter	≤5 mm
Rated current	16 A
Rated voltage	2,500 V
Rated impulse voltage	15 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C



Technical characteristics

Mating cycles	≥500		
---------------	------	--	--

Material properties

2 (pebble grey)
with exemption
per alloy containing up to 4 % lead by weight
with exemption
ined
ined
l-b94e-4e88-97a1-571845975242
5-2 (2020-08)
1-3) 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
	EN 50124-1
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	26.16 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019867
ETIM	EC000438

Product data sheet 09 14 002 3025 Han HV single module, 16A 2500V male



Commercial data

eCl@ss	27440217 Module for industrial connectors	(power/signals)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09140023025