

## R 15-EG-13,5



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 0101
Specification	R 15-EG-13,5
HARTING eCatalogue	<a href="https://b2b.harting.com/09150000101">https://b2b.harting.com/09150000101</a>

### Identification

Category	Hoods/Housings
Series	R 15
Type of hood/housing	Screw mounted housing
Description of hood/housing	Straight

### Version

Locking type	Screw locking
--------------	---------------

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)



Pushing Performance  
Since 1945

Material properties

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	10
Net weight	9.96 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021594
ETIM	EC003556
eCl@ss	27440224 Shell for circular connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09150000101](#)