

## Han Coax ETCS male insert



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 001 3004
Specification	Han Coax ETCS male insert
HARTING eCatalogue	<a href="https://b2b.harting.com/09150013004">https://b2b.harting.com/09150013004</a>

### Identification

Category	Inserts
Series	Han-Brid <sup>®</sup>
Identification	Han <sup>®</sup> Coax ETCS

### Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	1
further contacts	+ shielding
Details	Please order contacts separately.

### Technical characteristics

Rated current	16 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	$\geq 500$

### Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance

## Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	10
Net weight	8.84 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09150013004