

## Han D F crimp contact 0,14-0,37mm Au/HMC



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 200 6224
Specification	Han D F crimp contact 0,14-0,37mm Au/HMC
HARTING eCatalogue	<a href="https://b2b.harting.com/09152006224">https://b2b.harting.com/09152006224</a>

### Identification

Category	Contacts
Series	Han D <sup>®</sup> HMC
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Operating current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	8 mm
Mating cycles with other HMC components	≥10,000

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

## Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	100
Net weight	0.69 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09152006224](#)