

SEK CAB FLAT NSH RND AWG28/7 09P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 009 7008
Specification	SEK CAB FLAT NSH RND AWG28/7 09P 30,48m
HARTING eCatalogue	https://b2b.harting.com/09180097008

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

Version

Cable length	30.48 m
Number of cores	9
Core structure	AWG 28/7
Shielding	Unshielded

Technical characteristics

Impedance	100 Ω
Limiting temperature	-30 ... +75 °C unmoved -20 ... +75 °C moved
Conductor resistance @ 20 °C	$\leq 216 \Omega/\text{km}$

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UL 1581
	UL PLCC, CL2
CE	Yes

Commercial data

Packaging size	1
Net weight	700 g
Net weight	42 g/m
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140024274
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09180097008