

## SEK CAB FLAT COLOR TW AWG28/7 64P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 064 7006
Specification	SEK CAB FLAT COLOR TW AWG28/7 64P 30,48m
HARTING eCatalogue	<a href="https://b2b.harting.com/09180647006">https://b2b.harting.com/09180647006</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)
Description of the cable	Twisted pair

### Version

Cable length	30.48 m
Number of cores	64
Core structure	AWG 28/7

### Technical characteristics

Impedance	122 $\Omega$
Limiting temperature	-20 ... +105 °C
Signal run time @ 20 °C	$\leq 5.35$ ns/m

### Material properties

Material (cable)	PVC
Colour (cable)	Colour coded
Material flammability class acc. to UL 94	VW-1
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

UL / CSA	UL 758 AVL2.E42769
----------	--------------------

## Commercial data

Packaging size	1
Net weight	4,400 g
Net weight	113 g/m
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140025462
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09180647006