



Pushing Performance  
Since 1945

# SEK-18 SV MA LP ANG29 26P PL2




Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 18 526 6323  |
| Specification      | SEK-18 SV MA LP ANG29 26P PL2   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09185266323">https://b2b.harting.com/09185266323</a> |

## Identification

|                            |                 |
|----------------------------|-----------------|
| Category                   | Connectors      |
| Series                     | SEK Low-profile |
| Element                    | Male connector  |
| Description of the contact | Angled          |

## Version

|                    |   |
|--------------------|---|
| Termination method | Wave soldering termination                  |
| Connection type    | PCB to cable<br>Motherboard to daughtercard |
| Number of contacts | 26  |
| Termination length | 2.9 mm                                      |

## Technical characteristics

|                                    |                           |
|------------------------------------|---------------------------|
| Contact rows                       | 2                         |
| Contact spacing (termination side) | 2.54 mm                   |
| Rated current                      | 1 A                       |
| Insulation resistance              | $>10^9 \Omega$            |
| Contact resistance                 | $\leq 20 \text{ m}\Omega$ |
| Limiting temperature               | -55 ... +125 °C           |
| Insertion and withdrawal force     | $\leq 52 \text{ N}$       |
| Performance level                  | 2<br>acc. to IEC 60603-13 |
| Mating cycles                      | $\geq 250$                |



Pushing Performance  
Since 1945

## Technical characteristics

|                           |                               |
|---------------------------|-------------------------------|
| Test voltage $U_{r.m.s.}$ | 1 kV                          |
| Isolation group           | IIIa ( $175 \leq CTI < 400$ ) |

## Material properties

|   |  |
|---|--|
| Material (insert)                         | Thermoplastic resin (PBT)                                      |
| Colour (insert)                           | Grey   |
| Material (contacts)                       | Copper alloy   |
| Surface (contacts)                        | Noble metal over Ni Mating side<br>Sn over Ni Termination side |
| Material flammability class acc. to UL 94 | V-0  |
| RoHS                                      | compliant  |
| ELV status                                | compliant  |
| China RoHS                                | e  |
| REACH Annex XVII substances               | Not contained  |
| REACH ANNEX XIV substances                | Not contained  |
| REACH SVHC substances                     | Not contained  |
| California Proposition 65 substances      | Yes  |
| California Proposition 65 substances      | Antimony trioxide<br>Lead<br>Nickel                            |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08)   |
| Requirement set with Hazard Levels        | R26  |

## Specifications and approvals

|                        |  |
|------------------------|--|
| Specifications         | IEC 60603-13   |
| UL / CSA               | UL 1977 ECBT2.E102079<br>CSA-C22.2 No. 182.3 ECBT8.E102079 |
| Railway classification | F3/I3  |

## Commercial data

|                                |               |
|--------------------------------|---------------|
| Packaging size                 | 100           |
| Net weight                     | 5.2 g         |
| Country of origin              | Romania       |
| European customs tariff number | 85366990      |
| GTIN                           | 5713140031180 |

## Commercial data


ETIM

EC002637

eCl@ss

27460201 PCB connector (board connector)

## Cross section of solder termination



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09185266323](#)