



Pushing Performance  
Since 1945

# SEK-19 SV MA STD ANG29 RLG 10P PL3 CLIP




Image is for illustration purposes only. Please refer to product description.

Part number	09 19 510 7953
Specification	SEK-19 SV MA STD ANG29 RLG 10P PL3 CLIP
HARTING eCatalogue	<a href="https://b2b.harting.com/09195107953">https://b2b.harting.com/09195107953</a>

## Identification

Category	Connectors
Series	SEK Standard
Element	Male connector
Description of the contact	Angled

## Version

Termination method	Reflow soldering termination (THR)
Connection type	PCB to cable
Number of contacts	10
Termination length	2.9 mm
PCB fixing	With board locks
Locking type	With long levers

## Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	>10 <sup>9</sup> Ω
Contact resistance	≤20 mΩ
Limiting temperature	-55 ... +125 °C (during reflow soldering max. +240 °C for 60 s)
Insertion and withdrawal force	≤30 N
Performance level	3 acc. to IEC 60603-13



**Pushing Performance**  
Since 1945

## Technical characteristics

Mating cycles	≥50
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	II ( $400 \leq CTI < 600$ )
PCB thickness	1.6 mm

## Material properties

Material (insert)	Thermoplastic resin (PCT)
Colour (insert)	Beige
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	100
Net weight	4.76 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140036741



**Pushing Performance**  
Since 1945

## Commercial data


ETIM

EC002637

eCl@ss

27460201 PCB connector (board connector)

## Cross section of solder termination



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09195107953](#)