

# Han 3A Protect Cover, 1 Lever, Die Cast



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5421
Specification	Han 3A Protect Cover, 1 Lever, Die Cast
HARTING eCatalogue	<a href="https://b2b.harting.com/09200035421">https://b2b.harting.com/09200035421</a>

## Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for hoods
	Metal
	With fixing cord
	With seal

## Version

Size	3 A
Locking type	Single locking lever
Details	for mounted female insert

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

## Material properties

Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	1.525 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140038912
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09200035421](#)