

Han 3A Protect Cover Die Cast for Hood P



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5422
Specification	Han 3A Protect Cover Die Cast for Hood P
HARTING eCatalogue	https://b2b.harting.com/09200035422

Identification

Category	Accessories
Series of hoods/housings	Han A [®]
Type of accessory	Protection cover
Description of the accessory	for hoods
	Metal
	With fixing cord

Version

Size	3 A
Locking type	Single locking lever
Details	for mounted male insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	20 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140038929
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09200035422](#)