

## Han 3A-C/P-f.Hood-DL-seal-grey-w.cord



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5441
Specification	Han 3A-C/P-f.Hood-DL-seal-grey-w.cord
HARTING eCatalogue	<a href="https://b2b.harting.com/09200035441">https://b2b.harting.com/09200035441</a>

### Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for hoods
	Thermoplastic
	With fixing cord
	With seal

### Version

Size	3 A
Locking type	Single locking lever
Details	for mounted female insert or for mounted Han-Brid <sup>®</sup> insert

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR



**Pushing Performance**  
Since 1945

## Material properties

Material (locking)	Polyamide (PA)
Colour (locking)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	10.36 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140038974
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09200035441](#)