

Han 10A-Cover-Plastic 2Pins, f Easy-Lock



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 010 5402
Specification	Han 10A-Cover-Plastic 2Pins, f Easy-Lock
HARTING eCatalogue	https://b2b.harting.com/09200105402

Identification

Category	Accessories
Series of hoods/housings	Han A [®]
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	Thermoplastic

Version

Size	10 A
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	10 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140039520
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09200105402](#)