

## Han 6B-Metallkappe



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 006 5403
Specification	Han 6B-Metallkappe
HARTING eCatalogue	<a href="https://b2b.harting.com/09300065403">https://b2b.harting.com/09300065403</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Protection cover
Description of the accessory	for bearing pedestal

### Version

Size	06 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (accessories)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance  
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	47 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140044210
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300065403](#)