

## Han 10B-HBM-Rear Fit-SL-w/o frame



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 30 010 0398  |
| Specification      | Han 10B-HBM-Rear Fit-SL-w/o frame   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09300100398">https://b2b.harting.com/09300100398</a> |

### Identification

|                             |                          |
|-----------------------------|--------------------------|
| Category                    | Hoods/Housings           |
| Series of hoods/housings    | Han <sup>®</sup> B       |
| Type of hood/housing        | Bulkhead mounted housing |
| Description of hood/housing | Rear mounting            |
| Type                        | Low construction         |

### Version

|                            |   |
|----------------------------|---|
| Size                       | 10 B  |
| Locking type               | Single locking lever                              |
| Han-Easy Lock <sup>®</sup> | Yes   |
| Field of application       | Standard hoods/housings for industrial connectors |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65   |
| Type rating acc. to UL 50 / UL 50E     | 4  |
|  | 4X   |
|  | 12   |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast   |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 7037 (dust grey) |



**Pushing Performance**  
Since 1945

## Material properties

|  |   |
|--|---|
| Material (seal)  | NBR   |
| Material (locking)   | Polycarbonate (PC)<br>Stainless steel   |
| Colour (locking)   | RAL 7037 (dust grey)  |
| Material flammability class acc. to UL 94 (locking levers) | V-0   |
| RoHS   | compliant   |
| ELV status   | compliant   |
| China RoHS   | e   |
| REACH Annex XVII substances                                | Not contained   |
| REACH ANNEX XIV substances                                 | Not contained   |
| REACH SVHC substances                                      | Yes   |
| REACH SVHC substances                                      | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol<br>Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)  |
| Requirement set with Hazard Levels                         | R1 (HL 1-3)<br>R7 (HL 1-3)  |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 127.2 g                                  |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140164611                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300100398](#)