



Pushing Performance
Since 1945

Han B Protect Cover Die Cast for Hood Co



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 010 5427
Specification	Han B Protect Cover Die Cast for Hood Co
HARTING eCatalogue	https://b2b.harting.com/09300105427

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for cable to cable housing
	Metal
	With fixing cord

Version

Size	10 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	51 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140045361
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300105427](#)