



Pushing Performance
Since 1945

Han B Protect Cover Die Cast for Hoods P



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 016 5422
Specification	Han B Protect Cover Die Cast for Hoods P
HARTING eCatalogue	https://b2b.harting.com/09300165422

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for hoods
	Metal
	With fixing cord

Version

Size	16 B
Locking type	Double locking lever
Han-Easy Lock [®]	Yes

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (seal)	NBR
Material (locking)	Polycarbonate (PC)
	Stainless steel
Colour (locking)	RAL 7037 (dust grey)



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	80 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140046498
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300165422](#)