

## Han B Protect Cover Die Cast for Hood PG



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 024 5432
Specification	Han B Protect Cover Die Cast for Hood PG
HARTING eCatalogue	<a href="https://b2b.harting.com/09300245432">https://b2b.harting.com/09300245432</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> B
Type of accessory	Protection cover
Description of the accessory	for hoods Metal With fixing cord

### Version

Size	24 B
Locking type	Single locking lever
Han-Easy Lock <sup>®</sup>	Yes

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (seal)	NBR
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)



**Pushing Performance**  
Since 1945

## Material properties

Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	a4a9de28-6060-4c0d-b79b-5842f7db41be
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	107.8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048003
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300245432](#)