

## Han B Base SM HC plastic cover 2 x Pg36



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 048 0296
Specification	Han B Base SM HC plastic cover 2 x Pg36
HARTING eCatalogue	<a href="https://b2b.harting.com/09300480296">https://b2b.harting.com/09300480296</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Surface mounted housing
Description of hood/housing	With thermo-plastic cover
Type	High construction

### Version

Size	48 B
Version	Side entry
Cable entry	2x Pg 36
Locking type	Single locking lever
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated



**Pushing Performance**  
Since 1945

## Material properties

Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	1,275.32 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048294
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300480296](#)