



Pushing Performance  
Since 1945

# Han E M Crimp Contact Au 0.14-0.37 mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6117
Specification	Han E M Crimp Contact Au 0.14-0.37 mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09330006117">https://b2b.harting.com/09330006117</a>

## Identification

Category	Contacts
Series	Han E <sup>®</sup>
Type of contact	Crimp contact

## Version

Gender	Male
Contact identification	No groove
Manufacturing process	Turned contacts

## Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

## Commercial data

Packaging size	100
Net weight	1.249 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140049772
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09330006117](#)