

## Han P male crimp contact 2,5 mm2 (Ag)



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 000 6107
Specification	Han P male crimp contact 2,5 mm2 (Ag)
HARTING eCatalogue	<a href="https://b2b.harting.com/09350006107">https://b2b.harting.com/09350006107</a>

### Identification

Category	Contacts
Series	Han® PushPull (V14)
Type of contact	Crimp contact
Description of the contact	Straight

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	2.5 mm <sup>2</sup>
Conductor cross-section	AWG 14
Stripping length	6 mm
Mating cycles	≥500

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	IEC 61076-3-118
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	100
Net weight	0.92 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140053496
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09350006107](#)