

Han PushPull RJ45 housing with gasket



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 35 002 0321 |
| Specification | Han PushPull RJ45 housing with gasket |
| HARTING eCatalogue | https://b2b.harting.com/09350020321 |

Identification

| | |
|-----------------------------|--------------------------|
| Category | Connectors |
| Series | Han® PushPull (V14) |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | With integrated seal |

Version

| | |
|--------------|----------|
| Locking type | PushPull |
|--------------|----------|

Technical characteristics

| | |
|--|----------------|
| Limiting temperature | -40 ... +70 °C |
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |

Material properties

| | |
|---|---------------|
| Material (hood/housing) | Thermoplastic |
| Colour (hood/housing) | Black |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Naphthalene |

Specifications and approvals

| | |
|----------------|-----------------|
| Specifications | IEC 61076-3-117 |
| PROFINET | Yes |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 3.38 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140053618 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09350020321](#)