

Han 10B Ex-HBM-Double Lever



Image is for illustration purposes only. Please refer to product description.

Part number	09 36 010 1301
Specification	Han 10B Ex-HBM-Double Lever
HARTING eCatalogue	https://b2b.harting.com/09360101301

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] Ex
Type of hood/housing	Bulkhead mounted housing

Version

Size	10 B
Locking type	Double locking lever
Field of application	Connectors for explosion hazardous environments
Details	ATTENTION! Only to be used with Han [®] Ex inserts!

Technical characteristics

Limiting temperature	-20 ... +40 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 With cable gland

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Commercial data

Packaging size	1
Net weight	246.6 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140054868
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09360101301](#) [9360101301](#)