

Han HPR HPTC size 3 CS-protection cover



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 002 5412
Specification	Han HPR HPTC size 3 CS-protection cover
HARTING eCatalogue	https://b2b.harting.com/09400025412

Identification

Category	Accessories
Series of hoods/housings	Han® HPR HPTC
Type of accessory	Protection cover
Description of the accessory	for cable side

Version

Locking type	Screw locking
--------------	---------------

Technical characteristics

Tightening torque (screw locking)	5 Nm
Limiting temperature	-55 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	148 g
Country of origin	Taiwan
European customs tariff number	85389099
GTIN	5713140902961
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09400025412](#)