



Pushing Performance  
Since 1945

# Han HPR SP1-CM-SCL-without lanyard



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 40 011 5412  |
| Specification      | Han HPR SP1-CM-SCL-without lanyard  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09400115412">https://b2b.harting.com/09400115412</a> |

## Identification

|                              |   |
|------------------------------|---|
| Category                     | Accessories   |
| Series of hoods/housings     | Han® HPR  |
| Type of accessory            | Protection cover  |
| Description of the accessory | for bulkhead mounted housings<br>for panel feed through housing |

## Version

|              |   |
|--------------|---|
| Size         | SP1   |
| Locking type | Screw locking   |
| Details      | Please note that when using the metal protection cover the connectors only can be used without voltage applied or a reduced voltage of max. 2000V.<br>Please note that the use of the protection cover is needed to protect the Han® HC 650 / HC 800 when dropped acc. IEC 61984. |

## Technical characteristics

|  |  |
|--|--|
| Tightening torque (screw locking)      | 6 Nm   |
| Limiting temperature                   | -40 ... +125 °C                                |
| Degree of protection acc. to IEC 60529 | IP65<br>IP68<br>IP69 / IPX9K acc. to ISO 20653 |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12                                  |



**Pushing Performance**  
Since 1945

## Material properties

|                         |   |
|-------------------------|---|
| Material (hood/housing) | Aluminium die-cast<br>Corrosion resistant |
| Surface (hood/housing)  | Powder-coated                             |
| Colour (hood/housing)   | RAL 9005 (jet black)                      |
| Material (locking)      | Stainless steel                           |

## Specifications and approvals

|           |  |
|-----------|--|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | DNV GL   |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1                                      |
| Net weight                     | 72 g                                   |
| Country of origin              | China                                  |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140422292                          |
| ETIM                           | EC002314                               |
| eCl@ss                         | 27440208 Cap for industrial connectors |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09400115412](#)