



Pushing Performance
Since 1945

Han 16HPR-cover-CL-cord



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 016 5483
Specification	Han 16HPR-cover-CL-cord
HARTING eCatalogue	https://b2b.harting.com/09400165483

Identification

Category	Accessories
Series of hoods/housings	Han® HPR
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings With fixing cord

Version

Size	16 B
Locking type	Central locking lever (on the hood)

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
	IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	273 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140192072
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09400165483](#) [9400165483](#)