



Pushing Performance
Since 1945

RJ45 RJ45 plug Cat5, 4p IDC




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1100
Specification	RJ45 RJ45 plug Cat5, 4p IDC
HARTING eCatalogue	https://b2b.harting.com/09451511100

Identification

Category	Connectors
Series	HARTING RJ Industrial®
Element	Cable connector
Specification	Straight

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4
Pack contents	Hood with shielding
	Splicing element
	Cable gland
	Assembly instructions

Technical characteristics

Conductor cross-section	0.22 ... 0.32 mm² Stranded
	0.26 ... 0.32 mm² Solid
Conductor cross-section	AWG 24 ... AWG 22 Stranded
	AWG 23 ... AWG 22 Solid
Wire outer diameter	≤1.6 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-40 ... +70 °C
Relative humidity	95 % Non-condensing (operation)



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm
Vibration resistance	10-500 Hz, 10 g, 0.3 mm, 2h/axis 7.9 m/s ² acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 60603-7 Mating face ISO/IEC 11801 EN 50173-1 EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	20 g
Country of origin	Romania
European customs tariff number	85366990



Pushing Performance
Since 1945

Commercial data

GTIN	5713140059320
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09451511100](#)