



Pushing Performance
Since 1945

Han3A RJ45 10G Cat6A PFT insert 8p



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 200 1560
Specification	Han3A RJ45 10G Cat6A PFT insert 8p
HARTING eCatalogue	https://b2b.harting.com/09452001560

Identification

Category	Connectors
Series	RJ45
Element	Inserts

Version

Size	3 A
Shielding	Fully shielded, 360° shielding contact

Technical characteristics

Transmission characteristics	Cat. 6A Class EA up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	24.42 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059511
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09452001560](#)