



Pushing Performance
Since 1945

Han3M RJ45 Cat5 PFT 8p



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 215 1102
Specification	Han3M RJ45 Cat5 PFT 8p
HARTING eCatalogue	https://b2b.harting.com/09452151102

Identification

Category	Connectors
Series	RJ45
Element	Panel feed through
Specification	Straight

Version

Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Fixing	Screwable in cover plates

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance
Since 1945

Material properties

Colour (hood/housing)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	55 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059573
ETIM	EC002636
eCl@ss	27440113 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09452151102](#)