



Pushing Performance  
Since 1945

# Han3A RJ45 Cat5 coupler 8p



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 215 1107
Specification	Han3A RJ45 Cat5 coupler 8p
HARTING eCatalogue	<a href="https://b2b.harting.com/09452151107">https://b2b.harting.com/09452151107</a>

## Identification

Category	Connectors
Series	RJ45
Element	Double coupling
Specification	incl. installation frame metal

## Version

Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

## Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP67

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Grey



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel Naphthalene

## Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	127 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059603
ETIM	EC001264
eCl@ss	27440190 Industry connector (unspecified)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09452151107](#)