

HPP V4 Hybrid C-PFT set 4+3p straight



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 245 1300
Specification	HPP V4 Hybrid C-PFT set 4+3p straight
HARTING eCatalogue	https://b2b.harting.com/09452451300

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	Hybrid
Element	Panel feed trough set
Specification	Straight

Version

Termination method	Solder termination
Shielding	Unshielded
Number of contacts	7
Number of data contacts	4
Number of power contacts	3
Pack contents	incl. housing and female insert

Technical characteristics

Rated current	5 A
Rated voltage	48 V
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material flammability class acc. to UL 94	V-0
---	-----



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	10.3 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059856
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09452451300](#)